

Lifeline VIEW



Lifeline VIEW Semi-Automatic Defibrillator

FULL-COLOR VIDEO INSTRUCTION DELIVERS BREAKTHROUGH EASE-OF-USE

The Lifeline VIEW makes it easy for anyone — from first responders to untrained bystanders — to respond confidently and appropriately during an emergency. This revolutionary life-saving device combines a sleek, user-friendly design with military-grade specifications—including the most proven biphasic waveform. It's also the first and only AED with a full-color interactive display that shows step-by-step videos for performing CPR, rescue breathing and external defibrillation.

You can also be confident that the device will be easy to maintain and rescue ready. The Lifeline VIEW provides clear guidance for using and maintaining the device. Additionally, it has been designed to support upgrades and enhancements.

Like the original award-winning Defibtech AED, the Lifeline VIEW includes all the mission-critical features necessary to provide the most advanced cardiac treatment and exceeds the American Heart Association performance recommendations.

Lifeline VIEW Semi-Automatic Defibrillator

TECHNICAL SPECIFICATIONS *

DEFIBRILLATOR

TYPE Semi-Automatic external defibrillator	DISPLAY High-resolution color LCD
MODEL DDU-2300 series	VIDEO PROMPTS Full motion video On-screen text prompts
WAVEFORM Biphasic Truncated Exponential (Impedance compensated)	CPR COACHING Video and voice coaching On-demand video help
ENERGY Adult: 150 Joules Child / Infant: 50 Joules (Nominal into 50 Ohm load)	VOICE PROMPTS Extensive voice prompts guide user through operation of the unit
CONTROLS Lighted On/Off button Lighted Shock button	RESCUE PROTOCOL AHA 2005 Supports protocol updates by the user (password protected)
CHARGE TIME ** Less than 4 seconds (shock decision to shock)	

**Typical, with new battery at 25° C

PATIENT ANALYSIS SYSTEM

PATIENT ANALYSIS Automatically evaluates patient impedance for proper pad contact. Monitors signal quality and analyzes patient ECG for shockable/non-shockable rhythms.	SENSITIVITY/SPECIFICITY Meets AAMI-DF-80 specifications and AHA recommendations
--	---

BATTERY PACK

MODEL DBP-2003	CAPACITY ** 125 shocks or 8 hours continuous operation
POWER 12V, 2800 mAh	STANDBY LIFE ** 4 years
TYPE Lithium/Manganese Dioxide Disposable, recyclable, non-rechargeable	LOW BATTERY INDICATORS Visible Audible

**Typical, with new battery at 25° C

SELF TESTS

AUTOMATIC Automatic daily, weekly and monthly circuitry tests	USER-INITIATED Unit and battery pack system test initiated by the user
BATTERY INSERTION System integrity test on battery insertion	STATUS INDICATION Visual and audible indication of unit status
PAD PRESENCE Pads preconnected tested daily	STATUS SCREEN Unit self-test results Pads and battery information (status and expiration)

DEFIBRILLATION / MONITORING PADS

MODEL Adult – DDP-2001 Child / Infant – DDP-2002	SURFACE AREA 77 cm ² (nominal, each pad) 50 cm ² (nominal, each pad)
TYPE Pre-connected, single-use, non-polarized, disposable, self-adhesive electrodes with cable and connector	

EVENT DOCUMENTATION

INTERNAL EVENT RECORD Critical ECG segments and rescue event parameters are recorded (greater than 60 minutes) and can be downloaded to a removable data card	REMOVABLE STORAGE (optional) Up to 30 hours of ECG and event data storage (no audio option) or up to 3 hours of audio (audio option). ECG and event storage on a removable data card. Actual length of storage is dependent on card capacity.
PC-BASED EVENT REVIEW ECG with event tag display, and audio playback when available	USB PORT Event download and maintenance operations

ENVIRONMENTAL

TEMPERATURE Operating: 0 to 50°C (32 to 122°F) Standby: 0 to 50°C (32 to 122°F)	SHOCK / DROP ABUSE TOLERANCE MIL-STD-810F 516.5 Procedure IV 48 inches (1.2 meters), any edge, corner, or surface, in standby mode
RELATIVE HUMIDITY Operating / Standby: 5%-95% (non-condensing)	CRUSH TEST 1,000 pounds (450 kg)
ALTITUDE -500 to 15,000 ft (-150 to 4500 m) per MIL-STD-810F 500.4 Procedure II	SEALING / WATER RESISTANCE IEC60529 class IP55; Protected against dust and waterjets (battery pack installed)
VIBRATION Ground (MIL-STD-810F 514.5 Category 20) Helicopter (RTCA/DO-160D, Section 8.8.2, Cat R, Zone 2, Curve G) Jet Aircraft (RTCA/DO-160D Section 8, Cat H, Zone 2, Curves B & R)	ESD EN61000-4-2: (Open air up to 8kV or direct contact up to 6kV)
	EMC (Emission) CISPR 11 Group 1 Level B and FCC Part 15
	EMC (Immunity) IEC 61000-4-3 and IEC 61000-4-8

PHYSICAL

SIZE 7.3 x 9.5 x 2.3 Inches (18.5 x 24 x 5.8 cm)	WEIGHT Less than 3 lbs (1.4 kg) (with battery)
---	---

*Specifications subject to change without notice



DAC-2703-AE rev A